




# MAUSOGUARD™

*Easy-to-Handle Casket Entombment with Complete Seepage Shielding*

The Mausoguard consists of three primary components:

- 1 The lower tray:** Constructed from extremely durable high-molecular-weight polyethylene, the lower tray has a Diamond-Rail base and a Uni-Rolled upper edge for complete rigidity and a permanent seal to the upper enclosure.
- 2 The upper bag:** The cover is made from a seven-layered co-extruded film, which allows the family to view the casket safely. FDA-approved, it prevents oxygen and odor transmission.

- 3**  
The film cover attaches to the tray with a **two-part fastening system**, consisting of:



**The two-part seal**, which is both mechanical (rails) and chemical (tape), ensures that the cover will not separate from the tray over time.

**The locking rails:** are pre-drilled and attached with rivets, offering a mechanical clamp that reinforces the adhesive attachment between the upper enclosure and the rigid tray.


# MAUSOGUARD™

## STEPS TO INSTALL


- 1** Open bag inside tray box.  
Remove contents: 1 bag, 1 bag rivets,  
1 bag plastic BBs (BBs are used later  
by placing in 1st half of crypt for ease  
of sliding in sealed tray and contents)



- 2** Remove twist ties around locking rails and set rails aside.
- 3** Position tray on lift or ground.
- 4** Position casket in tray.
- 5** Unfold the bag and drape over casket. Align seams at the ends of the bag to the corners of the tray.



- 6** Pull the bag over the rolled edge of the tray for a distance of 1 1/2 inches. With the bag pulled over the rolled edge all the way around the tray, reach under the bag and gently pull protective backing off the tape. Press bag against exposed tape while continuing to remove the backing.



- 7** Reposition locking rails covering the bag at the rolled edge. Push rivets into the pre-drilled rail until rivet is flush with surface.

## DIMENSIONS

### Variants

### Inside

### Outside

#### **MGB**

84.50" x 27.75"  
(84 1/2" x 27 3/4")

86.375" x 30.125"  
(86 3/8" x 30 1/8")

#### **MGA**

86.625" x 29.25"  
(86 5/8" x 29 1/4")

87.25" x 30.875"  
(87 1/4" x 30 7/8")

#### **Oversized**

33.50' x 85.50"  
(33.1/2" x 85 1/2")

35.125" x 87.125"  
(35 1/8" x 87 1/8")